

## GOTECH "the best partner" to raise your competition

### GT-7051-NGBD 皮鞋剝離強度試驗機 Shoe Peeling Strength Tester

SATRA TM404、BS 5131-5.1、GB/T 3903.3

本機適用於成鞋鞋底與鞋幫之間剝離強度的試驗方法。將成鞋裝上鞋楦夾持在剝離試驗機上，以剝離刀將鞋底與鞋幫結合處剝開，測得剝開時所需力值為剝離力。根據剝離力和刀口寬度計算剝離強度。

The GT-7051-NGBD is designed to determine the peeling strength between outsole and upper. The peeling force is calculated based on the peeling force and edge width.



| 產品規範 Specification                | SATRA TM404、BS 5131-5.1            | GB/T 3903.3          |
|-----------------------------------|------------------------------------|----------------------|
| 刀口寬度 Width of cutter              | 22±1mm                             | 20±0.1mm 或 10±0.05mm |
| 刀口下行速度 Descending speed of cutter | 0~50mm/min                         | 20±2mm/min           |
| 剝離角度 Peeling angle                | 0~20°                              | 0~10°                |
| 容量 Capacity                       | 100kg                              |                      |
| 平板升降範圍 Slab movable range         | 40mm                               |                      |
| 顯示方式 Display                      | U20控制器 controller                  |                      |
| 重量(約) Weight (approx.)            | 45kg                               |                      |
| 體積(約) Dimension (approx.)         | 60×34×95cm                         |                      |
| 電源 Power                          | 1φAC 220V 50Hz (依國別或指定 or specify) |                      |

瞭解更多產品信息，請登錄我司網站 [www.gotech.biz](http://www.gotech.biz)